



Ultra-Portable















Palmtop Design:


Arjun weighs only 800 Grams with grip oriented weight distribution, which maximizes the efficiency of Ultrasonic testing with single hand operation freeing up user's other hand to manoeuvre the probe.

Ease of Use:

Arjun comes with only few keys for operation and menu navigation.

The menu architecture of Arjun makes the inspection easy and comfortable for any level of operator.





Display:

Arjun series flaw detectors come with high resolution (800×480 pixel) WVGA display. Excellent brightness and option of white background for best visibility in direct sunlight.

Display Rotation:

Display Rotation or Flip feature, is convenient for Left hander as well as Right hander.





Connectors:

Two Lemo Size 00 or Mini Lemo Connectors are fitted on the machine.

Connectivity and Data Storage:

Micro USB slot for data transfer facility

Micro SD card slot for data storage, expandable upto 32 GB

I/O port for Single Axis Encoder input and TTL output
for external monitor alarm









IP Sealing:

Mating joints are gasketed for protection against water, splash and dust. It is designed to comply with IP66.

Rugged and Durable:

Arjun is developed to perform in all indoor and outdoor industrial environment.

The durable and high industrial grade components incorporated in Arjun give you best protection for your inspection needs.

It is tested to meet international standards for optimized performance.





Battery and Charging:

World class high capacity Li-Ion battery which gives 8 hours of continuous operation with full charge. Arjun has special charging circuit for fast charging. Battery can be charged inside the machine as well as EXTERNALLY without engaging the machine by connecting a Charging Dock Station provided along with the machine. So using spare battery round the clock testing is possible.

Easy Replacement of Battery:

Battery Compartment has 'quick release fasteners' for easy and quick replacement of battery.





Standard Kit:


- Main unit Ultrasonic Flaw Detector model Arjun10/20/30.
- Rechargeable Li-Ion Battery pack MB-1 (7.2V, 4AH).
- I Charger cum mains adaptor AC-1 (100-250V, 50Hz-60Hz).
- I Charging Dock Station for external charging ABC-1.
- 8GB USB flash drive containing User Manual and data transfer software ArinSoft.
- USB ON the Go (OTG) cable for data transfer.
- Neck Strap for extra protection.
- Pelican type carrying case.






Measurement resolution:

Measurement resolution of 0.01mm for better accuracy. Two independent gates with amplitude measurement up to 125% FSH.






DAC:

Auto Plotting standard dynamic DAC/TCG for easy defect evaluation. Multiple curves with user selectable dB intervals (1dB to 14dB). Any of the curves can be selected as flaw monitor gate.

*Onboard DGS/AVG:

Onboard DGS/AVG for defect size evaluation. Echo signals are evaluated in reference with standard DGS/AVG associated with particular probe type and material being tested.






*AWS D1.1:

Built in Software for AWS which provides dynamic reflector indication ratings for various AWS weld inspections . This allows efficient inspection by eliminating manual calculations.

**Encoder Input:


Single Axis Encoder Input for Real time probe positioning (mm/Inch).

- * Available only in Arjun 20 & Arjun 30.
- **Available only in Arjun30.











UT Data Recording:

It comes with the continuous **UT Data Recording** facility with **Colour Flaw Plotting**. Upto 100 Hours of UT Data Recording (A-Scan and Colour B-Scan) can be stored on 8GB Micro SD card. It comes with **Non-Tamperable Date/Time** stamp, which is best for **Evidence Based Testing**. Options of Playback and Analysis of A-Scan and colour B-Scan for analysis on main unit of Arjun are available.

Analysis:

Recorded data can be transferred to PC using USB cable or USB OTG Cable for Analysis, After the test data are transferred to PC, analysis is possible using ArjnSoft software.





Reporting, Printing and Documentation:


Reports in PDF and WORD format can be generated from A-Scan and colour B-Scan recorded files with all essential information like operator details, job details, and defect details for subsequent printing and documentation

** Available only in Arjun30



Pulser/Receiver Characteristics






Dead Zone/Near Surface Resolution in Angle Probe:


Angle Probe: 4MHz, 70 Degree.

Reflection from 1.5mm SDH from V1 Block

Dead Zone/Near Surface Resolution in Normal Probe:

Normal Probe: 4MHz, 10mm Dia. Reflection from 5mm Step of VW Block.







Dead Zone/Near Surface Resolution in TR Probe:

Twin Crystal Probe: 4MHz, 10mm Dia. Reflection from 3mm Step of VW Block.

Far Surface Resolution:

Normal Probe: 4MHz, 10MM Diameter on V1 Block Resolution Notch.





Penetration Power:

Normal Probe: 2MHz, 24MM Diameter on V1 Block Perspex insert. Total number of back wall reflections are 6 full and 7th about 40% FSH with noise level about 10% FSH.

Sensitivity:

Normal Probe: 4MHz, 10mm Dia. Reflection From 1/64" (0.4mm diameter) FBH of ASTM Standard block









Time Base :		
Test Range	ij.	2.5 mm to 5 meter (in steel). Fine mode
(Arjun10, Arjun20)		adjustable in step of 1mm.
Test Range	2	2.5 mm to 10 meter (in steel). Fine mode
(Arjun30)		adjustable in step of 1mm.
Velocity	*	1000 m/s to 15000 m/s. In Hot key mode it
		has 21 pre-set values. Fine mode adjustable
		in step of 1 m/s.
Delay	1	Up to 120mm adjustable in 0.01, 0.1mm or
		1mm step.
Horizontal Linearity	:	Non Linearity ±0.5%
Unit of Measurement	3	Metric (mm) and Inch
Pulser/receiver :		
TxPulse	*	Square wave pulse
PRF		50Hz to 1KHz coupled with test range in three
		adjustments
Gain		100 dB calibrated gain adjustable in 0.1, 0.5,
		1, 2, 6 or 14 dB step
Test Modes		Pulse echo and Transmit/Receive
Rectification	*	Full wave rectification with filtering.
Partial Rejection	:	0 to 125% FSH with LED indicator
Frequency Range	*	Broad Band amplifier (0.5 MHz to 15 MHz)
Vertical Linearity	*	Non Linearity ±3%
Connectors	÷	Lemo 00 (2 Nos.)
Monitor Gates :		
Independent Gates	*	Two fully independent gates GATEa and
		GATEb for flaw echo monitoring and
		thickness/distance measurement. Start and
		Width adjustable over full screen. Threshold
		level adjustable over 0 to 100% FSH.
Measurement Mode	t	Peak and Flank.
Display :		
LCD		5 inch Colour Wide VGA LCD display
		(800x480 pixel, size 108x64 mm) with
		five different colour sets.
Update Rate		60Hz Display rate.
Reference Waveform	***	Reference A-Scan pattern of standard test
		object can be saved and recalled in the
		object can be saved and recalled in the background for easy comparison during
Video Filled	•	background for easy comparison during
Video Filled Video Dynamic	4	background for easy comparison during testing
- The state of the		background for easy comparison during testing Solid filled echo patterns for better visibility.
- The state of the		background for easy comparison during testing Solid filled echo patterns for better visibility. Dynamic echo patterns which saves the last
Video Dynamic		background for easy comparison during testing Solid filled echo patterns for better visibility. Dynamic echo patterns which saves the last maximized echo amplitude for reference.

settings and custom probe set-ups, ERS (Equivalent Reflector Size) can also be displayed on the screen in mm/inch. *AWS D1.1 : Built in Software for rating of defects in accordance with AWS Specification D1.1 **UT Data Recording : Built-In : Carries out 100 Hours of continuous UT Data Recording (on SD Card) which can be replayed and analysed in machine as well as PC Colour Flaw Plotting/ : Real time Colour coded Encoded/Un-Encoded Colour B-Scan colour B-Scan along with A-Scan on the Screen which can be transferred to PC, Also analysis of A-Scan and B-Scan can be done in the machine as well as PC. Memory : Micro SD Card Slot : SD Card slot for all standard micro SD cards (up-to 32 GB) supported. A-Scan : 500 A-Scan can be saved in internal memory and Huge A-Scan storage capacity on SD Card depending on SD Card size. General : Size : 117 x 176 x 56 mm (HxWxD) Weight : 800 grams with Li-lon battery Battery : Hi capacity 7.2V, 4AH Lithium lon battery Battery Life : 8 Hours when fully charged Charging Method : Internal with power adaptor. (Standard) Charging Method : Externally with charging docking station and	Standard Software Op	tio	ns :	
*On-board DGS/AVG : Defect size evaluation using predefined probesettings and custom probeset-ups, ERS (Equivalent Reflector Size) can also be displayed on the screen in mm/inch. *AWS D1.1 : Built in Software for rating of defects in accordance with AWS Specification D1.1 **UT Data Recording : Built-In : Carries out 100 Hours of continuous UT Data Recording (on SD Card) which can be replayed and analysed in machine as well as PC Colour Flaw Plotting/ : Real time Colour coded Encoded/Un-Encoder colour B-Scan can be transferred to PC, Also analysis of A-Scan and B-Scan can be done in the machine as well as PC. Memory : Micro SD Card Slot : SD Card slot for all standard micro SD cards (up-to 32 GB) supported. A-Scan : 500 A-Scan can be saved in internal memory and Huge A-Scan storage capacity on SD card depending on SD Card size. General : Size : 117 x 176 x 56 mm (HxWxD) Weight : 800 grams with Li-Ion battery Battery : Hi capacity 7.2V, 4AH Lithium Ion battery Battery Life : 8 Hours when fully charged Charging Method : Internal with power adaptor. (Standard) Charging Method : Externally with charging docking station and	DAC	İ	Dynamic DAC curve can be digitally plotted (Smooth parabolic curve) on screen with selectable additional offset curves from 0 to 14 dB in 0.1 dB selectable steps. DAC curve can be set as flaw monitor gate. DAC curve can be plotted using minimum	
settings and custom probe set-ups, ERS (Equivalent Reflector Size) can also be displayed on the screen in mm/inch. *AWS D1.1 : Built in Software for rating of defects in accordance with AWS Specification D1.1 **UT Data Recording : Built-In : Carries out 100 Hours of continuous UT Data Recording (on SD Card) which can be replayed and analysed in machine as well as PC Colour Flaw Plotting/ : Real time Colour coded Encoded/Un-Encoded Colour B-Scan colour B-Scan along with A-Scan on the Screen which can be transferred to PC, Also analysis of A-Scan and B-Scan can be done in the machine as well as PC. Memory : Micro SD Card Slot : SD Card slot for all standard micro SD cards (up-to 32 GB) supported. A-Scan : 500 A-Scan can be saved in internal memory and Huge A-Scan storage capacity on SD Card depending on SD Card size. General : Size : 117 x 176 x 56 mm (HxWxD) Weight : 800 grams with Li-lon battery Battery : Hi capacity 7.2V, 4AH Lithium lon battery Battery Life : 8 Hours when fully charged Charging Method : Internal with power adaptor. (Standard) Charging Method : Externally with charging docking station and	*TCG	0.772	THE LANCE OF THE PROPERTY OF T	
**UT Data Recording: Built-In : Carries out 100 Hours of continuous UT Data Recording /dynamic A-Scan and B-Scan recording (on SD Card) which can be replayed and analysed in machine as well as PC Colour Flaw Plotting/ : Real time Colour coded Encoded/Un-Encoded colour B-Scan along with A-Scan on the Screen which can be transferred to PC, Also analysis of A-Scan and B-Scan can be done in the machine as well as PC. Memory: Micro SD Card Slot : SD Card slot for all standard micro SD cards (up-to 32 GB) supported. A-Scan : 500 A-Scan can be saved in internal memory and Huge A-Scan storage capacity on SD Card depending on SD Card size. General: Size : 117 x 176 x 56 mm (HxWxD) Weight : 800 grams with Li-Ion battery Battery Life : 8 Hours when fully charged Charging Method : Internal with power adaptor. (Standard) Charging Method : Externally with charging docking station and	*On-board DGS/AVG	Ti.	(Equivalent Reflector Size) can also be	
Built-In : Carries out 100 Hours of continuous UT Data Recording /dynamic A-Scan and B-Scan recording	*AWS D1.1	216	The Auto-Company of the Auto-Company	
Built-In : Carries out 100 Hours of continuous /dynamic A-Scan and B-Scan recording (on SD Card) which can be replayed and analysed in machine as well as PC Colour Flaw Plotting/: Real time Colour coded Encoded/Un-Encoded Colour B-Scan colour B-Scan along with A-Scan on the Screen which can be transferred to PC, Also analysis of A-Scan and B-Scan can be done in the machine as well as PC. Memory: Micro SD Card Slot : SD Card slot for all standard micro SD cards. (up-to 32 GB) supported. A-Scan : 500 A-Scan can be saved in internal memory and Huge A-Scan storage capacity on SD Card depending on SD Card size. General: Size : 117 x 176 x 56 mm (HxWxD) Weight : 800 grams with Li-lon battery Battery : Hi capacity 7.2V, 4AH Lithium lon battery Battery Life : 8 Hours when fully charged Charging Method : Internal with power adaptor. (Standard) Charging Method : Externally with charging docking station and	**UT Data Recording	1	•	
(on SD Card) which can be replayed and analysed in machine as well as PC Colour Flaw Plotting/ : Real time Colour coded Encoded/Un-Encoded Colour B-Scan along with A-Scan on the Screen which can be transferred to PC, Also analysis of A-Scan and B-Scan can be done in the machine as well as PC. Memory: Micro SD Card Slot : SD Card slot for all standard micro SD cards (up-to 32 GB) supported. A-Scan : 500 A-Scan can be saved in internal memory and Huge A-Scan storage capacity on SD Card depending on SD Card size. General: Size : 117 x 176 x 56 mm (HxWxD) Weight : 800 grams with Li-Ion battery Battery : Hi capacity 7.2V, 4AH Lithium Ion battery Battery Life : 8 Hours when fully charged Charging Method : Internal with power adaptor. (Standard) Charging Method : Externally with charging docking station and	Built-In		Carries out 100 Hours of continuous	
Colour B-Scan colour B-Scan along with A-Scan on the Screen which can be transferred to PC, Also analysis of A-Scan and B-Scan can be done in the machine as well as PC. Memory: Micro SD Card Slot : SD Card slot for all standard micro SD cards. (up-to 32 GB) supported. A-Scan : 500 A-Scan can be saved in internal memory and Huge A-Scan storage capacity on SD Card depending on SD Card size. General: Size : 117 x 176 x 56 mm (HxWxD) Weight : 800 grams with Li-lon battery Battery : Hi capacity 7.2V, 4AH Lithium lon battery Battery Life : 8 Hours when fully charged Charging Method : Internal with power adaptor. (Standard) Charging Method : Externally with charging docking station and	UT Data Recording		(on SD Card) which can be replayed and	
Screen which can be transferred to PC, Also analysis of A-Scan and B-Scan can be done in the machine as well as PC. Memory: Micro SD Card Slot : SD Card slot for all standard micro SD cards. (up-to 32 GB) supported. A-Scan : 500 A-Scan can be saved in internal memory and Huge A-Scan storage capacity on SD Card depending on SD Card size. General: Size : 117 x 176 x 56 mm (HxWxD) Weight : 800 grams with Li-lon battery Battery : Hi capacity 7.2V, 4AH Lithium lon battery Battery Life : 8 Hours when fully charged Charging Method : Internal with power adaptor. (Standard) Charging Method : Externally with charging docking station and	Colour Flaw Plotting/		Real time Colour coded Encoded/Un-Encoded	
Micro SD Card Slot : SD Card slot for all standard micro SD cards. (up-to 32 GB) supported. A-Scan : 500 A-Scan can be saved in internal memory and Huge A-Scan storage capacity on SD Card depending on SD Card size. General: Size : 117 x 176 x 56 mm (HxWxD) Weight : 800 grams with Li-lon battery Battery : Hi capacity 7.2V, 4AH Lithium lon battery Battery Life : 8 Hours when fully charged Charging Method : Internal with power adaptor. (Standard) Charging Method : Externally with charging docking station and	Colour B-Scan		Screen which can be transferred to PC, Also analysis of A-Scan and B-Scan can be done	
(up-to 32 GB) supported. A-Scan : 500 A-Scan can be saved in internal memory and Huge A-Scan storage capacity on SD Card depending on SD Card size. General: Size : 117 x 176 x 56 mm (HxWxD) Weight : 800 grams with Li-lon battery Battery : Hi capacity 7.2V, 4AH Lithium Ion battery Battery Life : 8 Hours when fully charged Charging Method : Internal with power adaptor. (Standard) Charging Method : Externally with charging docking station and	Memory :			
and Huge A-Scan storage capacity on SD Card depending on SD Card size. General: Size : 117 x 176 x 56 mm (HxWxD) Weight : 800 grams with Li-lon battery Battery : Hi capacity 7.2V, 4AH Lithium Ion battery Battery Life : 8 Hours when fully charged Charging Method : Internal with power adaptor. (Standard) Charging Method : Externally with charging docking station and	Micro SD Card Slot		SD Card slot for all standard micro SD cards. (up-to 32 GB) supported.	
Size : 117 x 176 x 56 mm (HxWxD) Weight : 800 grams with Li-lon battery Battery : Hi capacity 7.2V, 4AH Lithium lon battery Battery Life : 8 Hours when fully charged Charging Method : Internal with power adaptor. (Standard) Charging Method : Externally with charging docking station and	A-Scan	***		
Weight : 800 grams with Li-Ion battery Battery : Hi capacity 7.2V, 4AH Lithium Ion battery Battery Life : 8 Hours when fully charged Charging Method : Internal with power adaptor. (Standard) Charging Method : Externally with charging docking station and	General :			
Battery : Hi capacity 7.2V, 4AH Lithium Ion battery Battery Life : 8 Hours when fully charged Charging Method : Internal with power adaptor. (Standard) Charging Method : Externally with charging docking station and	Size	*)	117 x 176 x 56 mm (HxWxD)	
Battery Life : 8 Hours when fully charged Charging Method : Internal with power adaptor. (Standard) Charging Method : Externally with charging docking station and	Weight	200	800 grams with Li-lon battery	
Charging Method : Internal with power adaptor. (Standard) Charging Method : Externally with charging docking station and	Battery		Hi capacity 7.2V, 4AH Lithium Ion battery	
(Standard) Charging Method : Externally with charging docking station and	Battery Life		8 Hours when fully charged	
	(10) (20)	:	Internal with power adaptor.	
(External) power adaptor.	Charging Method (External)	1000	Externally with charging docking station and power adaptor.	
Power Adaptor : Charger cum mains adaptor AC-1 (100-250V, 50Hz-60Hz).	Power Adaptor	1648	CONTROL CONTRO	
Software : ArjnSoft Software for Data Transfer, Analysis Reporting, Documentation and Printing.	Software	***	ArjnSoft Software for Data Transfer, Analysis, Reporting, Documentation and Printing.	
Temperature : Operating temperature 0 to 55°	Temperature	F. (1)	Operating temperature 0 to 55°	

^{*} Available only in Arjun 20 & Arjun30. **Available only in Arjun30.



Arjun Series Comparison



Technical Parameters	Arjun10	Arjun20	Arjun30
Palmtop, Ultralight, Weighs only 800 Gms along with Battery.	√	√	√
Test Range 2.5mm to 5 metre (In steel).	√	√	√
Gain 100 dB adjustable in step of 0.1, 0.5, 1, 2, 6, or 14 dB Step.	√	√	√
MicroSD Card Slot (Upto 32GB).	√	√	√
USB On The Go communication Port.	√	√	√
Dynamic DAC which can be easily plotted on the Screen.	√	√	√
Selection Of British and Metric Units.	√	√	√
Lithium Ion Battery Pack 7.2VDC, 4AH which gives 8+ hours of battery life.	√	√	√
High Resolution 5 inch Colour WVGA LCD/TFT display (800 \times 480 pixel, Size 108 \times 64 mm).	√	√	√
Internal memory of 500 A-Scan patterns and 50 Calibration Setups.	√	√	√
Reporting and Printing in A4 format is possible.	√	√	√
TTL Output	×	√	√
TCG (Time Corrected Gain) for Echo Amplitude Compensation.	×	√	√
Built-in DGS/AVG Curves for time proven flaw size evaluation.	×	√	√
Built-In Software for Flaw Rating as per AWS Standards.	×	√	√
Test Range 2.5mm to 10 metre (In steel).	×	√	√
Continuous UT Data Recording.	×	×	√
Colour Coded B-Scan along with recording facility.	×	×	√
Single Axis Encoder Input.	×	×	√
100 of Hours of UT Data Recording which can be transferred to PC.	×	×	√
A-Scan and B-Scan Data Analysis inside the machine as well as PC.	×	×	√







On hinged stand



Leather wrist strap



Mounted on the tripod



Designed, Developed and Manufactured by:

MODSONIC INSTRUMENTS MFG. CO. (P) LTD

Plot No.33, Phase III, GIDC Industrial Estate, Naroda, Ahmedabad-382 330, INDIA, Tele: +91 (79), 4890 8054, 2281 1217, 22813131, Fax: +91(079)22820012 modsonic@modsonic.com, www.modsonic.com